CGY770Rセッティングシート

| CGY770Rセッティ フライヤー | | | | 寛規 | 見選 | | | | | | | | | | |
|----------------------|--|-----------|-----|------|--------|-------------|--------|--------|----------|-------|---------|-----|------------|-----------|----------|
| 機体名 | Prodrone PDH-02C | | | | | | | | | | | | | | |
| MOTOR | EP or GP | | | | | | | | | | | | | | |
| メインローター | - | | | EP 7 | | | 735 mm | | | | | | | | |
| サーボタイプ | AIL HC7 | | | 1C70 | 01 ELE | | | HC701 | | | PIT | | HC701 | | |
| | R | RUD HT7 | | | 00 | <u> </u> | | | | | | | <u> </u> | | |
| | <u>, </u> | HOV | | | AIL | 60 | % | ELE | 62 | % | RUD | 100 | % | | |
| 送信機/AFRレート | | IDL1 | | | AIL | 90 | % | ELE | 85 | % | RUD | | % | | |
| | | IDL2 | | | AIL | 90 | % | ELE | 85 | % | RUD | | % | | |
| | | IDL3 | | | AIL | 90 | % | ELE | 85 | % | RUD | | % | | |
| | | HOLD | | | AIL | 60 | % | ELE | 62 | % | RUD | | % | | |
| 送信機/EXPレート |] | | HOV | | AIL | 0 | % | ELE | 0 | % | RUD | 0 | % | | |
| | | IDL1 | | | AIL | -10 | % | ELE | 0 | % | RUD | 0 | % | | |
| | | IDL2 | | | AIL | -10 | % | ELE | 0 | % | RUD | 0 | % | | |
| | | IDL3 | | | AIL | -10 | % | ELE | 0 | % | RUD | 0 | % | | |
| | | HOLD | | | AIL | -10 | % | ELE | 0 | % | RUD | 0 | % | | |
| ジャイロゲイン | | HOV | | | AIL | 89 | % | ELE | 89 | % | RUD | 90 | % | | |
| | | IDL1 | | | AIL | 79 | % | ELE | 80 | % | RUD | | % | | |
| | | IDL2 | | | AIL | 79 | % | ELE | 80 | % | RUD | | % | | |
| | | IDL3 | | | AIL | 79 | % | ELE | 80 | % | RUD | | % | | |
| | <u> </u> | HOLD | | | AIL | 65 | % | ELE | 60 | % | RUD | 40 | % | | |
| ローター回転数(RPM) | HOV | | | 1200 | | IDI | IDL1 | | 1730 | | IDL2 | | 1730 | | |
| |] [| IDL3 173 | | |) | | | | | | | | | | |
| シ゛ャイロコンテ゛ィション | Cı | HOV C | | C2 | Н | ΟV | C3 | HOV C4 | | C 4 | IDL1 | | C5 IDL1 | | .1 |
| フニノレエ ソ | | | | | | | | | | | | | | | |
| フライトチューン | C 1 | 150 | % | | 150 | % | ا ما | 150 | % | ا م ا | 90 | % | ا د دا | 00 | % |
| ベースゲイン CYC. レート | C1 | 150 60 | d/s | C2 | | d/s | | 60 | % d/s | | 230 | d/s | ł | 90 230 | % d/s |
| ワーキングモード | | | CMT | 02 | or | | AVC | | or | | Norm | | C 3 | 230 | u/ S |
| AIL.セパレーション | _ | | | pnt | l | | 100 | | l oi | | 1401111 | u i | J | | |
| cnt.ゲインAIL | _ C1 | 5 | % | C2 | | % | Сз | 5 | % | C 4 | 20 | % | C 5 | 20 | % |
| cnt.ゲインELE | C1 | 5 | % | C2 | | % | C3 | | % | | 40 | % | C5 | | % |
| エキスポネンシャル | C1 | -5 | % | C2 | | % | C3 | | % | | -20 | % | ł | -20 | % |
| レスポンス.スタイル | C1 | 17 | n | ł | 17 | n | | 17 | n | | 10 | n | C 5 | | n |
| スタビリティゲイン | C1 | | | C2 | | | C3 | | | C 4 | | | C 5 | | |
| ELE.ホセイ.ハイ | C1 | 0 | % | C2 | 0 | % | Сз | 0 | % | C 4 | 0 | % | C 5 | 0 | % |
| ELE.ホセイ.ロー | C1 | 0 | % | C2 | 0 | % | СЗ | 0 | % | C 4 | 0 | % | C 5 | 0 | % |
| ハイピッチゲイン | _ | 0 | % | | | | • ' | | | • ' | | | | | |
| | - | | | - | | | | | | | | | | | |













